External AC-DC Power Supplies Selector Guide

Wall Mount Adapters

5W to 10W



VFR05
- 5W
- 55.1 x 37.0 x 42.9mm
- Level VI & CoC Tier 2
- LPS approved
- Changeable input plugs



VFL05
- 5W
- 55.1 x 24.1 x 35.5mm
- Level VI & CoC Tier 2
- LPS approved
- Low cost



ACM06
- 6W
- 73.5 x 30.7 x 42.5mm
- Level VI & CoC Tier 2
- 2 x MOPP
- Optional white case



VEU10
- 2.1A USB A socket
- 50.8 x 37.0 x 22.0mm
- Level VI & CoC Tier 2
- Low cost
- Class II

12W



ACM12
- 12W
- 76.0 x 30.3 x 48.2mm
- Level VI & CoC Tier 2
- 2 x MOPP
- Optional white case



VEL12
- 12W
- 76.0 x 29.5 x 39.4mm
- Level VI & CoC Tier 2
- LPS approved
- Low cost



VER12
- 12W
- 76.5 x 41.0 x 37.6mm
- Level VI & CoC Tier 2
- LPS approved
- Changeable input plugs

18W



AMF18
- 18W
- 90.5 x 33.5 x 58.5mm
- Home healthcare approval
- 2 x MOPP
- Optional white case



ACM18
- 18W
- 88.0 x 30.0 x 49.5mm
- Level VI & CoC Tier 2
- 2 x MOPP
- Optional white case



VEL18
- 18W
- 90.0 x 34.0 x 47.5mm
- Level VI & CoC Tier 2
- LPS approved
- Low cost

24W



AMF24
- 24W
- 90.5 x 33.5 x 58.5mm
- Home healthcare approval
- 2 x MOPP
- Optional white case



ACM24
- 24W
- 88.0 x 30.0 x 57.0mm
- Level VI & CoC Tier 2
- 2 x MOPP
- Optional white case



VEL24
- 24W
- 90.0 x 34.0 x 47.5mm
- Level VI & CoC Tier 2
- LPS approved
- Low cost



VER24
- 24W
- 90.5 x 42.0 x 42.7mm
- Level VI & CoC Tier 2
- LPS approved
- Changeable input plugs

36W to 100W



AMF36
- 36W
- 90.5 x 33.5 x 58.5mm
- Home healthcare approval
- 2 x MOPP
- Optional white case



ACM36
- 36W
- 96.7 x 33.0 x 59.5mm
- Level VI & CoC Tier 2
- 2 x MOPP
- Optional white case



VEL36
- 36W
- 94.0 x 35.0 x 46.6mm
- Level VI & CoC Tier 2
- LPS approved
- Low cost



VER36
- 36W
- 94.5 x 47.0 x 43.9mm
- Level VI & CoC Tier 2
- LPS approved
- Low cost



PGW65
- 65W
- 90.5 x 58.5 x 33.5mm
- Power Delivery protocol
- Home healthcare approval
- IP22 rating



PGW100
- 100W
- 97.0 x 57.0 x 34.0mm
- Power Delivery protocol
- Home healthcare approval
- IP22 rating

Desktop

36W to 60W



AKM36
- 36W
- 108.0 x 50.0 x 33.8mm
- Level VI & CoC Tier 2
- 2 x MOPP
- Optional white case



AEK40
- 40W
- 107.0 x 47.0 x 30.1mm
- Level VI & CoC Tier 2
- 5V to 48V outputs
- Class I



VEC40
- 40W
- 116.3 x 52.4 x 31.3mm
- Level VI & CoC Tier 2
- CCC qualified
- LPS approved



AKM45
- 45W
- 122.4 x 51.4 x 31.5mm
- Home healthcare approval
- 2 x MOPP
- Optional white case



VEC50
- 50W
- 116.3 x 52.4 x 31.3mm
- Level VI & CoC Tier 2
- CCC Qualified
- LPS approved



AEK60
- 60W
- 118.0 x 47.0 x 30.1mm
- Level VI & CoC Tier 2
- <0.15W standby power
- Class I

65W to 70W



AKM65
- 65W
- 125.0 x 62.3 x 34.0mm
- Home healthcare approval
- 2 x MOPP
- Optional white case



ALM65
- 65W
- 116.3 x 52.4 x 31.3mm
- Level VI
- 2 x MOPP
- Class I & II



VEC65
- 65W
- 116.3 x 52.4 x 31.3mm
- Level VI & CoC Tier 2
- CCC qualified
- LPS approved



AEJ70
- 70W
- 120.0 x 52.0 x 31.0mm
- Level VI & CoC Tier 2
- 65°C operation
- Class I

85W to 100W



ALM85
- 85W
- 116.3 x 52.4 x 31.3mm
- Level VI & CoC Tier 2
- 2 x MOPP
- IP32 rating



VES90
- 90W
- 139.0 x 58.0 x 31.0mm
- Level VI & CoC Tier 2
- CCC qualified
- Low cost



AKM90
- 90W
- 125.0 x 62.3 x 34.0mm
- CoC Tier 2, EU2019/1782
- 2 x MOPP
- Class I & II



AJM90
- 90W
- 140.0 x 71.0 x 22.0mm
- Level VI
- Slim profile
- Class II



PGD100
- 100W
- 114.5 x 56.5 x 32.0mm
- Power Delivery protocol
- Home healthcare approval
- IP22 rating



AEJ100
- 100W
- 141.0 x 58.0 x 39.5mm
- Level VI & CoC Tier 2
- 65°C operation
- Active PFC

120W to 160W



ALM120
- 120W
- 140.0 x 71.0 x 22.0mm
- Level VI & CoC Tier 2
- CCC qualified
- 2 x MOPP



VES120
- 120W
- 168.0 x 71.0 x 37.5mm
- Level VI & CoC Tier 2
- CCC qualified
- Low cost



PGD140
- 140W
- 121.0 x 65.8 x 32.0mm
- Power Delivery protocol
- Home healthcare approval
- IP22 rating



ALM150
- 150W
- 186.0 x 72.0 x 38.0mm
- Home healthcare approval
- IP32 rating
- Class I & II

AEJ160
- 160W
- 150.0 x 70.0 x 38.0mm
- Level VI & CoC Tier 2
- 65°C operation
- Active PFC

200W

AQM200
- 200W
- 166.5 x 54.2 x 33.0mm
- Home healthcare approval
- IP22 rating
- Class I & II

ALM200
- 200W
- 209.0 x 82.0 x 43.0mm
- Home healthcare approval
- IP32 rating
- Class I & II

250W

AQM250
- 250W
- 173.0 x 67.0 x 32.0mm
- Home healthcare approval
- IP22 rating
- Class I & II

AHM250
- 250W
- 223.0 x 88.5 x 38.6mm
- Level V
- IP22 rating
- Low profile

300W to 450W

AQM300
- 300W
- 183.0 x 85.0 x 35.0mm
- Home healthcare approval
- IP22 rating
- Class I & II

VES300
- 300W
- 197.4 x 88.9 x 39.0mm
- Level VI & CoC Tier 2
- CCC qualified
- Low cost

AQM450
- 450W
- 254 x 116 x 47mm
- Medical 2x MOPP
- IP22 rating
- Class I

Recently introduced | Medical version available | Home healthcare approval

For full specifications visit: **www.xppower.com**

2025