




本公司智慧財產 ,未經同意不得複製
Diptronics copyright,
may not be used without permission from Diptronics.











Specifications:
1.Rating: 50uA 5V DC/50mA 18V DC
2.Initial contact resistance: 100mΩ Max.
3.Insulation resistance: 100MΩ Min. 500V DC
4.Withstand Voltage: 500V AC for 1 minute.
5.Operating force: 200±50gf.
6.Operating life: 300,000cycles Min.
7.General tolerances ±0.4mm

ZONE	REV.	DESCRIPTION	DATE	APPD.
1	A	DWG.REL.	2025.01.23	張志瑋

DIPTRONICS 圜達 2025.02.04 ISSUED R&D DEPT

APPD: 2025/02/03	020401 - 張志瑋	Q'TY:	
CHKD: 2025/02/03	020401 - 張志瑋	SCALE:	4:1
DR: 2025/02/03	980502 - 陳秋柱	REV: A	UNITS: mm
DESIGN: 2023/04/19	980502 - 陳秋柱		

圜達實業股份有限公司
DIPTRONICS MANUFACTURING INC.

PART NO:	ESL-PMGQR	MAT'L:	
		FINISH:	

PART NAME: ESL-PMGQR
DWG NO: