




本公司智慧財產 ,未經同意不得複製
Diptronics copyright,
may not be used without permission from Diptronics.
















切斷後底部(基準線)至端子腳高度





Amber

NOTE:
RATING MIN/MAX : 0.1mA-100mA, 20mVDC-32VDC
MAX POWER:1.0VA
CONTACT RESISTANCE : 150mΩ MAX
INSULATION RESISTANCE : 100MΩ min,500VDC
DIELECTRIC STRENGTH : 250VAC for 1 Minute
OPERATING LIFE : 25,000 cycles
OPERATING TEMPERATURE : -40°C~85°C at 96% RH Max
OPERATING FORCE: 400±120gf
TOTAL TRAVELS: 2.4±0.3mm
GENERAL TOLERANCE（公差）：±0.25mm

DIPTRONICS 圓達 2026.07.29 ISSUED R&D DEPT

ZONE	REV.	DESCRIPTION	DATE	APPD.
3	C	依工變26138新增熱銲形狀	2026.07.24	林后謙
2	B	依工變26138新增鐳雕字樣&熱銲形狀	2026.06.15	林后謙
1	A	DWG REL.	2026.01.27	林后謙

APPD: 林后謙	Q'TY:	圓達實業股份有限公司 DIPTRONICS MANUFACTURING INC.	PART NAME: ILLUMINA;TED SWITCH
CHKD: 陳瞳柏	SCALE: 4:1		
DR: 2026.07.24 CYH	REV: C UNITS: mm	PART NO: MLG-5GHA4BAVR-TA	MAT'L:
DESIGN: 930201 - WILLSON			FINISH:
			DWG NO: MLG-5GHA4BAVR-TA