STRADA-2X2R-T2

Reflector-based optic design with extremely low glare (luminous intensity class as good as G6) and high efficiency. IESNA Type II (medium) beam applicable for pedestrian and road lighting from low poles.



SPECIFICATION:

Dimensions	50.0 x 50.0
Height	11.4 mm
Fastening	pin, screw
ROHS compliant	yes

MATERIALS:


Component	Type	Material	Colour	Finish	Coating
STRADA-2X2R-T2	Reflector	PC	metal		HMDS


ORDERING INFORMATION:

Component	Qty in box	MOQ	MPQ	Box weight (kg)
C19761_STRADA-2X2R-T2 » Box size: 480 x 280 x 300 mm	504	504	28	5.6

LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

REV	DATE
003	19.03.2025





See www.ledil.com/support for more installation detail

PART	TYPE	MATERIAL	COLOR / COATING
C19761_STRADA-2x2-5050-T2-R_007_Mechmodel_003	Reflector	PC	Metal

MECHANICAL DRAWING

PRODUCT Strada

LEDiL

Plastic moulding general tolerances according to DIN 16901-130 and applies if not otherwise shown in the drawing. Silicone moulding general tolerances according to ISO 3302-1 Class M3 and applies if not otherwise shown in the drawing.

FIRST ANGLE PROJECTION:

This drawing is the property of LEDiL Oy. It may not be copied or otherwise distributed without prior written permission from LEDiL Oy.

SCALE 1:1 | WEIGHT - | A4 SHEET 1/1

See also our general installation guide: www.ledil.com/installation_guide

LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy
Joensuunkatu 7
FI-24100 SALO
Finland

LEDiL Inc.
228 West Page Street
Suite D
Sycamore IL 60178
USA

Ledil Optics Technology (Shenzhen) Co., Ltd.
405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support
www.ledil.com/
where_to_buy

Shipping locations
Poznan, Poland
Hong Kong, China

Distribution Partners
www.ledil.com/
where_to_buy

LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.