Outdoor
UHF/700/800+GNSS Direct Mount 2-in-1 Antenna

SKF450758L125DM(W) – 440-470 / 750-960 MHz GNSS L1, L2, L5



Features & Applications:

- *Vehicle roof mount, directly on metal plane*
- *Port 1; 440-470 / 750-960MHz*
- *Port 2; Active GNSS L1, L2 & L5 with low noise 30dB amplifier*
- *Cable / length; RG-58 / 17ft (5.2m)*
- *GNSS Cable / length; RG-174 / 17ft (5.2m)*
- *Connector; SMA-Male*
- *Available in Black (P/N SKF450758L125DM) or White (P/N SKF450758L125DMW)*
- *Heavy and light vehicles*
- *IoT, navigation, tracking*

Electrical specifications @ 25° C					
Frequency Band – 440-470 / 750-960 MHz					
Antenna type	**Nominal Impedance**	**Polarization**	**Radiation pattern**	**Power withstanding**	**DC Ground**
Dipole	50Ω	Vertical	Omni	45W	Yes

Frequency (MHz)	**440-470**	**750-960**
VSWR W/17FT (5.2M) Cable	2.5:1	2:1
Avg. Peak Gain (dBi)	3.3	3.5
Avg. Efficiency (%)	66	60
HPBW Vertical Plane (°)	36	42

GNSS Antenna: Frequency Bands – L1, L2 & L5			
Frequency (MHz)	**L1: 1561-1602**	**L2: 1215-1237**	**L5: 1164-1189**
Return Loss (dB)	< -10	< -13	< -15
Gain – Radiating Element (dBic)	3.6	0.3	-0.4
Average Efficiency (%)	70	60	46
LNA Gain (dB) Typical	28	33	30
Noise Figure (dB)	1.7 @ 1575MHz	2.2 @ 1227MHz	2.2 @ 1164MHz
Polarization	RHCP		
Operating Voltage (V)	2.5 - 18		
Power Consumption	Max. 16mA		

Mechanical Specifications				
SKF450758L125DM				
Size W/H/L	**Color**	**Weight**	**Cable / Connector Type**	**Fixing System**
52.5 (2.07”) x 63.6 (2.50”) x 178.3 (7.02”) mm	Black	375grms (0.83lbs)	RG-58 / SMA-Male RG-174 / SMA-Male	Direct Mount
Housing Material	**Operating Temperature**	**Storage Temperature**	**Ingress Protection**	**RoHS-6 Compliant**
UV Protected Plastic	-40°C to +85°C	-40°C to +85°C	IP67	Yes


Notes:
1. Measured on Ø52in (1.3m) ground plane.
2. Requires Ø.875” (22.3mm) hole.


Test Setup / Charts


SKF450758L125DM





antenna sample measured on
Ø52in (1.3m) ground plane




















LNA Gain and out-of-band rejection.



L1 RHCP Pattern




L2 + L5 RHCP Pattern



Mechanical Drawing

SKF450758L125DM



Dimensions: Inches (mm)
Unless otherwise specified, all tolerances are ±.020 (0.5mm)

Packaging

SKF450758L125DM

1 antenna packed in a plastic bag.
1 label on each plastic bag with part number, description, date code.

Notes:

1. Please contact sales for availability, lead time, and/or any special requests. Samples available upon request.
2. Similar product: SKF490758L125DM (UHF band 470-512MHz).

For More Information:
Americas - antennas.us@pulseelectronics.com | Europe – antennas.eu@pulseelectronics.com | Asia – antennas.as@pulseelectronics.com | Questions? +1-800-ANTENNA
Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright , 2020. Pulse Electronics, Inc. All rights reserved.
Company address: Pulse Electronics, a YAGEO Company, 15255 Innovation Drive, Suite #100, San Diego, CA 92128
'YAGEO Corporation and its affiliates do not recommend the use of commercial, automotive, and/or COTS grade products for high reliability applications or manned space flight.'