
KEMET Part Number: CKC21C682JJGACAUTO

KC Link Auto C0G, Ceramic, DC Link. 0.0068 uF, 5%, 1700V, C0G, SMD, MLCC. High Voltage. Ultra-Stable, Low Loss, 2220



General Information	
Supplier:	KEMET
Series:	KC Link Auto C0G
Style:	SMD Chip
Description:	SMD, MLCC, High Voltage, Ultra-Stable, Low Loss
Features:	Ultra-Stable, Low Loss
RoHS:	Yes
Termination:	Tin
Failure Rate:	N/A
Chip Size:	2220

Dimensions	
L	5.70 ± 0.40 mm
W	5.00 ± 0.40 mm
T	2.50 ± 0.20 mm
B	0.6 ± 0.35 mm

Specifications	
Capacitance:	0.0068 uF
Capacitance Tolerance:	5%
Voltage DC:	1700 VDC
Dielectric Withstanding Voltage:	2040 V
Temperature Range:	-55/+150C
Temperature Coefficient:	C0G
Dissipation Factor:	0.10% 1kHz 25C
Aging Rate:	0% Loss/Decade Hour
Insulation Resistance:	100 Gohms

Packaging Specifications	
Packaging:	T&R, 180mm, Plastic Tape
Packaging Quantity:	500

Rev. 6/6/18

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

© 2006 - 2018 IntelliData.net