
Automotive Dual N-Channel 60 V (D-S) 175 °C MOSFETs

PowerPAK® SO-8L Dual Asymmetric



FEATURES


- TrenchFET® power MOSFET
- AEC-Q101 qualified
- 100 % R_g and UIS tested
- Optimized for synchronous buck applications
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

AUTOMOTIVE GRADE

Pb-free

RoHS COMPLIANT

HALOGEN FREE



PRODUCT SUMMARY		
	N-CHANNEL 1	N-CHANNEL 2
V_{DS} (V)	60	60
$R_{DS(on)}$ (Ω) at V_{GS} = 10 V	0.0200	0.0086
I_D (A)	20	54
Configuration	Dual	
Package	PowerPAK SO-8L asymmetric	

ABSOLUTE MAXIMUM RATINGS (T_C = 25 °C, unless otherwise noted)					
PARAMETER		SYMBOL	N-CHANNEL 1	N-CHANNEL 2	UNIT
Drain-source voltage		V_{DS}	60	60	V
Gate-source voltage		V_{GS}	± 20		
Continuous drain current	T_C = 25 °C	I_D	20 [a]	54	A
	T_C = 125 °C		15	31	
Continuous source current (diode conduction)		I_S	20 [a]	44	
Pulsed drain current [b]		I_{DM}	65	90	
Single pulse avalanche current	L = 0.1 mH	I_{AS}	19	31	
Single pulse avalanche energy		E_{AS}	18	48	mJ
Maximum power dissipation [b]	T_C = 25 °C	P_D	27	48	W
	T_C = 125 °C		9	16	
Operating junction and storage temperature range		T_J, T_{stg}	-55 to +175		°C
Soldering recommendations (peak temperature) [d, e]			260		

THERMAL RESISTANCE RATINGS					
PARAMETER		SYMBOL	N-CHANNEL 1	N-CHANNEL 2	UNIT
Junction-to-ambient	PCB mount [c]	R_{thJA}	85	85	°C/W
Junction-to-case (drain)		R_{thJC}	5.5	3.1	

Notes

a. Package limited
b. Pulse test; pulse width ≤ 300 µs, duty cycle ≤ 2 %
c. When mounted on 1" square PCB (FR4 material)
d. See solder profile (www.vishay.com/doc?73257). The PowerPAK SO-8L is a leadless package. The end of the lead terminal is exposed copper (not plated) as a result of the singulation process in manufacturing. A solder fillet at the exposed copper tip cannot be guaranteed and is not required to ensure adequate bottom side solder interconnection
e. Rework conditions: manual soldering with a soldering iron is not recommended for leadless components

For technical questions, contact: automostechsupport@vishay.com

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

SPECIFICATIONS (T_C = 25 °C, unless otherwise noted)								
PARAMETER	**SYMBOL**	**TEST CONDITIONS**			**MIN.**	**TYP.**	**MAX.**	**UNIT**
Static								
Drain-source breakdown voltage	V_{DS}	V_{GS} = 0 V, I_D = 250 µA		N-Ch 1	60	-	-	V
		V_{GS} = 0 V, I_D = 250 µA		N-Ch 2	60	-	-	
Gate-source threshold voltage	$V_{GS(th)}$	V_{DS} = V_{GS}, I_D = 250 µA		N-Ch 1	2.5	3.0	3.5	
		V_{DS} = V_{GS}, I_D = 250 µA		N-Ch 2	2.5	3.0	3.5	
Gate-source leakage	I_{GSS}	V_{DS} = 0 V, V_{GS} = ± 20 V		N-Ch 1	-	-	± 100	nA
				N-Ch 2	-	-	± 100	
Zero gate voltage drain current	I_{DSS}	V_{GS} = 0 V	V_{DS} = 60 V	N-Ch 1	-	-	1	µA
		V_{GS} = 0 V	V_{DS} = 60 V	N-Ch 2	-	-	1	
		V_{GS} = 0 V	V_{DS} = 60 V, T_J = 125 °C	N-Ch 1	-	-	50	
		V_{GS} = 0 V	V_{DS} = 60 V, T_J = 125 °C	N-Ch 2	-	-	50	
		V_{GS} = 0 V	V_{DS} = 60 V, T_J = 175 °C	N-Ch 1	-	-	250	
		V_{GS} = 0 V	V_{DS} = 60 V, T_J = 175 °C	N-Ch 2	-	-	250	
On-state drain current [a]	$I_{D(on)}$	V_{GS} = 10 V	V_{DS} ≥ 5 V	N-Ch 1	15	-	-	A
		V_{GS} = 10 V	V_{DS} ≥ 5 V	N-Ch 2	30	-	-	
Drain-source on-state resistance [a]	$R_{DS(on)}$	V_{GS} = 10 V	I_D = 6 A	N-Ch 1	-	0.0165	0.0200	Ω
		V_{GS} = 10 V	I_D = 10 A	N-Ch 2	-	0.0071	0.0086	
		V_{GS} = 10 V	I_D = 6 A, T_J = 125 °C	N-Ch 1	-	-	0.0320	
		V_{GS} = 10 V	I_D = 10 A, T_J = 125 °C	N-Ch 2	-	-	0.0135	
		V_{GS} = 10 V	I_D = 6 A, T_J = 175 °C	N-Ch 1	-	-	0.0390	
		V_{GS} = 10 V	I_D = 10 A, T_J = 175 °C	N-Ch 2	-	-	0.0167	
Forward transconductance [b]	g_{fs}	V_{DS} = 10 V, I_D = 6 A		N-Ch 1	-	24	-	S
		V_{DS} = 10 V, I_D = 10 A		N-Ch 2	-	98	-	
Dynamic [b]								
Input capacitance	C_{iss}	V_{GS} = 0 V	V_{DS} = 25 V, f = 1 MHz	N-Ch 1	-	687	1000	pF
		V_{GS} = 0 V	V_{DS} = 25 V, f = 1 MHz	N-Ch 2	-	1490	2100	
Output capacitance	C_{oss}	V_{GS} = 0 V	V_{DS} = 25 V, f = 1 MHz	N-Ch 1	-	313	500	
		V_{GS} = 0 V	V_{DS} = 25 V, f = 1 MHz	N-Ch 2	-	777	1100	
Reverse transfer capacitance	C_{rss}	V_{GS} = 0 V	V_{DS} = 25 V, f = 1 MHz	N-Ch 1	-	10	15	
		V_{GS} = 0 V	V_{DS} = 25 V, f = 1 MHz	N-Ch 2	-	21	30	
Total gate charge [c]	Q_g	V_{GS} = 10 V	V_{DS} = 30 V, I_D = 1.5 A	N-Ch 1	-	9.2	16	nC
		V_{GS} = 10 V	V_{DS} = 30 V, I_D = 3 A	N-Ch 2	-	19.2	32	
Gate-source charge [c]	Q_{gs}	V_{GS} = 10 V	V_{DS} = 30 V, I_D = 1.5 A	N-Ch 1	-	3.2	-	
		V_{GS} = 10 V	V_{DS} = 30 V, I_D = 3 A	N-Ch 2	-	6.3	-	
Gate-drain charge [c]	Q_{gd}	V_{GS} = 10 V	V_{DS} = 30 V, I_D = 1.5 A	N-Ch 1	-	0.8	-	
		V_{GS} = 10 V	V_{DS} = 30 V, I_D = 3 A	N-Ch 2	-	1.5	-	
Gate resistance	R_g	f = 1 MHz		N-Ch 1	0.35	0.74	1.20	Ω
				N-Ch 2	0.20	0.42	0.65	

For technical questions, contact: automostechsupport@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

SPECIFICATIONS (T_C = 25 °C, unless otherwise noted)							
PARAMETER	**SYMBOL**	**TEST CONDITIONS**		**MIN.**	**TYP.**	**MAX.**	**UNIT**
Dynamic [b]							
Turn-on delay time [c]	$t_{d(on)}$	V_{DD} = 30 V, R_L = 20 Ω, $I_D \cong$ 1.5 A, V_{GEN} = 10 V, R_g = 1 Ω	N-Ch 1	-	11	18	ns
		V_{DD} = 30 V, R_L = 10 Ω, $I_D \cong$ 3 A, V_{GEN} = 10 V, R_g = 1 Ω	N-Ch 2	-	12	25	
Rise time [c]	t_r	V_{DD} = 30 V, R_L = 20 Ω, $I_D \cong$ 1.5 A, V_{GEN} = 10 V, R_g = 1 Ω	N-Ch 1	-	2	5	
		V_{DD} = 30 V, R_L = 10 Ω, $I_D \cong$ 3 A, V_{GEN} = 10 V, R_g = 1 Ω	N-Ch 2	-	3	5	
Turn-off delay time [c]	$t_{d(off)}$	V_{DD} = 30 V, R_L = 20 Ω, $I_D \cong$ 1.5 A, V_{GEN} = 10 V, R_g = 1 Ω	N-Ch 1	-	16	30	
		V_{DD} = 30 V, R_L = 10 Ω, $I_D \cong$ 3 A, V_{GEN} = 10 V, R_g = 1 Ω	N-Ch 2	-	20	40	
Fall time [c]	t_f	V_{DD} = 30 V, R_L = 20 Ω, $I_D \cong$ 1.5 A, V_{GEN} = 10 V, R_g = 1 Ω	N-Ch 1	-	8	15	
		V_{DD} = 30 V, R_L = 10 Ω, $I_D \cong$ 3 A, V_{GEN} = 10 V, R_g = 1 Ω	N-Ch 2	-	11	18	
Source-Drain Diode Ratings and Characteristics [b]							
Pulsed current [a]	I_{SM}		N-Ch 1	-	-	65	A
			N-Ch 2	-	-	90	
Forward voltage	V_{SD}	I_F = 6 A, V_{GS} = 0 V	N-Ch 1	-	0.82	1.2	V
		I_F = 10 A, V_{GS} = 0 V	N-Ch 2	-	0.80	1.2	
Body diode reverse recovery time	t_{rr}	I_F = 4 A, di/dt = 100 A/µs	N-Ch 1	-	22	45	ns
		I_F = 5 A, di/dt = 100 A/µs	N-Ch 2	-	41	85	
Body diode reverse recovery charge	Q_{rr}	I_F = 4 A, di/dt = 100 A/µs	N-Ch 1	-	15	30	nC
		I_F = 5 A, di/dt = 100 A/µs	N-Ch 2	-	36	75	
Reverse recovery fall time	t_a	I_F = 4 A, di/dt = 100 A/µs	N-Ch 1	-	12	-	ns
		I_F = 5 A, di/dt = 100 A/µs	N-Ch 2	-	19	-	
Reverse recovery rise time	t_b	I_F = 4 A, di/dt = 100 A/µs	N-Ch 1	-	10	-	
		I_F = 5 A, di/dt = 100 A/µs	N-Ch 2	-	22	-	
Body diode peak reverse recovery current	$I_{RM(REC)}$	I_F = 4 A, di/dt = 100 A/µs	N-Ch 1	-	-1.3	-	A
		I_F = 5 A, di/dt = 100 A/µs	N-Ch 2	-	-1.6	-	


Notes

a. Pulse test; pulse width ≤ 300 µs, duty cycle ≤ 2 %
b. Guaranteed by design, not subject to production testing
c. Independent of operating temperature


Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

For technical questions, contact: automostechsupport@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000


N-CHANNEL 1 TYPICAL CHARACTERISTICS (T_A = 25 °C, unless otherwise noted)




Output Characteristics




Transconductance




Transfer Characteristics



Capacitance




On-Resistance vs. Drain Current




Gate Charge

For technical questions, contact: automostechsupport@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000


N-CHANNEL 1 TYPICAL CHARACTERISTICS (T_A = 25 °C, unless otherwise noted)




Source Drain Diode Forward Voltage




On-Resistance vs. Gate-to-Source Voltage




Threshold Voltage



Drain Source Breakdown vs. Junction Temperature




On-Resistance vs. Junction Temperature




Safe Operating Area

For technical questions, contact: automostechsupport@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

N-CHANNEL 1 TYPICAL CHARACTERISTICS (T_A = 25 °C, unless otherwise noted)



Normalized Thermal Transient Impedance, Junction-to-Ambient



Normalized Thermal Transient Impedance, Junction-to-Case


Note

- The characteristics shown in the graph:
  - Normalized Transient Thermal Impedance Junction-to-Ambient (25 °C)


  is given for general guidelines only to enable the user to get a “ball park” indication of part capabilities. The data are extracted from single pulse transient thermal impedance characteristics which are developed from empirical measurements. The latter is valid for the part mounted on printed circuit board - FR4, size 1" x 1" x 0.062", double sided with 2 oz. copper, 100 % on both sides. The part capabilities can widely vary depending on actual application parameters and operating conditions

For technical questions, contact: automostechsupport@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000


N-CHANNEL 2 TYPICAL CHARACTERISTICS (T_A = 25 °C, unless otherwise noted)




Output Characteristics




Transconductance




Transfer Characteristics



Capacitance




On-Resistance vs. Drain Current




Gate Charge

For technical questions, contact: automostechsupport@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000


N-CHANNEL 2 TYPICAL CHARACTERISTICS (T_A = 25 °C, unless otherwise noted)




Source Drain Diode Forward Voltage




On-Resistance vs. Gate-to-Source Voltage




Threshold Voltage



Drain Source Breakdown vs. Junction Temperature




On-Resistance vs. Junction Temperature




Safe Operating Area

For technical questions, contact: automostechsupport@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

N-CHANNEL 2 TYPICAL CHARACTERISTICS (T_A = 25 °C, unless otherwise noted)



Normalized Thermal Transient Impedance, Junction-to-Ambient



Normalized Thermal Transient Impedance, Junction-to-Case

Note


- The characteristics shown in the graph:
  - Normalized Transient Thermal Impedance Junction-to-Ambient (25 °C)

  is given for general guidelines only to enable the user to get a “ball park” indication of part capabilities. The data are extracted from single pulse transient thermal impedance characteristics which are developed from empirical measurements. The latter is valid for the part mounted on printed circuit board - FR4, size 1" x 1" x 0.062", double sided with 2 oz. copper, 100 % on both sides. The part capabilities can widely vary depending on actual application parameters and operating conditions

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package / tape drawings, part marking, and reliability data, see www.vishay.com/ppg?75486.

For technical questions, contact: automostechsupport@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

PowerPAK® SO-8L Assymetric Case Outline



DIM.	MILLIMETERS			INCHES		
	MIN.	NOM.	MAX.	MIN.	NOM.	MAX.
A	1.00	1.07	1.14	0.039	0.042	0.045
A1	0.00	0.06	0.13	0.000	0.003	0.005
b	0.33	0.41	0.48	0.013	0.016	0.019
b1	0.44	0.51	0.58	0.017	0.020	0.023
b2	4.80	4.90	5.00	0.189	0.193	0.197
b3	0.04	0.12	0.20	0.002	0.005	0.008
c	0.20	0.25	0.30	0.008	0.010	0.012
D	5.00	5.13	5.25	0.197	0.202	0.207
D1	4.80	4.90	5.00	0.189	0.193	0.197
D2	3.63	3.73	3.83	0.143	0.147	0.151
D3	0.81	0.91	1.01	0.032	0.036	0.040
D4	1.98	2.08	2.18	0.078	0.082	0.086
D5	1.47	1.57	1.67	0.058	0.062	0.066
e	1.20	1.27	1.34	0.047	0.050	0.053
E	6.05	6.15	6.25	0.238	0.242	0.246
E1	4.27	4.37	4.47	0.168	0.172	0.176
E2	2.75	2.85	2.95	0.108	0.112	0.116
E3	1.89	1.99	2.09	0.074	0.078	0.082
F	0.05	0.12	0.19	0.002	0.005	0.007
L	0.62	0.72	0.82	0.024	0.028	0.032
L1	0.92	1.07	1.22	0.036	0.042	0.048
K	0.41	0.51	0.61	0.016	0.020	0.024
K1	0.64	0.74	0.84	0.025	0.029	0.033
K2	0.54	0.64	0.74	0.021	0.025	0.029
W	0.13	0.23	0.33	0.005	0.009	0.013
W1	0.31	0.41	0.51	0.012	0.016	0.020
W2	2.72	2.82	2.92	0.107	0.111	0.115
W3	2.86	2.96	3.06	0.113	0.117	0.120
W4	0.41	0.51	0.61	0.016	0.020	0.024
θ	5°	10°	12°	5°	10°	12°

DWG: 6009


Note

- Millimeters will govern

For technical questions, contact: pmostechsupport@vishay.com

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

RECOMMENDED MINIMUM PADs FOR PowerPAK® SO-8L DUAL ASYMMETRIC



Recommended Minimum Pads
Dimensions in mm [inches]

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, “Vishay”), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay’s knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer’s responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer’s technical experts. Product specifications do not expand or otherwise modify Vishay’s terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

© 2019 VISHAY INTERTECHNOLOGY, INC. ALL RIGHTS RESERVED