INTRODUCING

MINI WIDEBAND CELLULAR ANTENNAS

- **Cost effective**
- **Screw mount and SMA connections available**
- **Operates well on compact ground planes**
- **Compact and rugged**



Mini wideband cellular whip antennas are rugged, low-cost and easy to install. They have a low-profile radome which makes them ideal for discrete mounting. The antennas offer wideband cellular coverage of 617-5000 MHz which makes them suitable for a wide range of applications.

KEY BENEFITS

- Cost effective wideband cellular antenna options
- Straight and right-angle options
- Low profile/height (50mm / 1.97 in.)
- High gain and efficiency
- Compact and rugged

APPLICATIONS

- Cellular coverage 617-5000 MHz
- Low power devices
- Internet of Things (IoT) devices
- Hand-held devices
- Remote control
- Monitoring and sensing

ELECTRICAL

Full electrical specification available in product datasheets

ENVIRONMENTAL SPECIFICATIONS

- Operating & Storage Temperature °C (°F) - -30 to +75°C (-22 to +167°F)
- Material Substance Compliance - RoHS, CE and UKCA Compliant

MECHANICAL

- Dimensions – h x d – mm (in.) - Varies by Model
- Weight - g. (lbs) - Varies by Model

LEARN MORE

2487514-1 Datasheet (Straight)

2487805-1 Datasheet (Right Angle)

Customer Presentation

TE Connectivity, TE and TE connectivity (logo) are trademarks.