
ENTRELEC
Electrical Solutions
By TE Connectivity

INTRODUCING

WIRING DUCTS

- **Wiring duct covers hold securely even in a vertical position and under vibration**
- **Smooth, burr-free edges protect installers from injury and wires from damage**



The ENTRELEC wiring duct range includes popular profile widths such as 24, 40, 60, 80 100, and 120 mm.

The high-quality PVC & halogen-free material allows the use in many applications such as standard industrial applications with PVC range to the most demanding applications such as railways, high buildings, industrial enclosures, and public buildings with the low smoke and halogen-free range. The specific design offers many solutions to help optimize and simplify the wiring.

KEY BENEFITS

- Flame-retardant, self-extinguishing according to UL94-V0
- Save time while breaking off ribs without using any tools
- Additional holes on the side, allow the use of cable ties to group your cables in an efficient manner
- Speeds up your maintenance work with our cover design that eases cover removal
- Quickly mount wire retainers on the bottom rail of the duct without a screw and slide them along the rail
- Speed up your project and easy to install

APPLICATIONS

- Control cabinet and data center
- Railway
- Battery energy storage solutions and electric vehicle infrastructure
- Warehouse automation
- Semiconductor manufacturing equipment
- High buildings
- Elevators

ELECTRICAL

- PVC: Operating temperature: -5°C to 60°C
- LSHF: Operating temperature: -25°C to 90°C

MECHANICAL

- PVC wiring duct: from 25 mm to 120 mm wide & 30 mm to 100 mm height
- LSHF (Low Smoke Halogen Free): from 25 mm to 80 mm wide and 30 mm to 80 mm height

MATERIALS

- PVC & halogen-free

STANDARDS AND SPECIFICATIONS

HL3
EN 45545-2

LEARN MORE

- Wiring duct landing page
- Wiring duct brochure
- Wiring duct partlist
- Wiring duct images

ENTRELEC, TE Connectivity, TE and TE connectivity (logo) are trademarks.